

GAMA DE BOMBAS SP

BGP SUBFACTORY
2020

P/N	Descripción	Motor	Tensión	Arranque	Standard Comp. Kit , Rp2 1/2" SP17	QTD	Stage Package Kit SP17	QTD	Length dependent kits	QTD		
12A01910	SP17-10 Rp2½ 4"3X380-415/50 5.5kW	MS4000	3x400V	DOL	0012HH00	1	0012HH06	9	0012H410	1		
12A01913	SP17-13 Rp2½ 6"3X380-415/50 7.5kW	MS6000	3x400V	DOL	0012HH01	1	0012HH06	12	0012H613	1		
12A01917	SP17-17 Rp2½ 6"3X380-415/50 9.2kW	MS6000	3x400V	DOL	0012HH01	1	0012HH06	16	0012H617	1		
12A01920	SP17-20 Rp2½ 6"3X380-415/50 11kW	MS6000	3x400V	DOL	0012HH02	1	0012HH06	19	0012H020	1		
12A01924	SP17-24 Rp2½ 6"3X380-415/50 13kW	MS6000	3x400V	DOL	0012HH02	1	0012HH06	23	0012H024	1		
12A01927	SP17-27 Rp2½ 6"3X380-415/50 15kW	MS6000	3x400V	DOL	0012HH02	1	0012HH06	26	0012H627	1		
P/N	Descripción	Motor	Tensión	Arranque	Standard Comp. Kit , Rp3" SP30	QTD	Stage Package Kit SP30	QTD	Length dependent kits	QTD		
13A01901	SP30- 1 Rp3 4"3X380-415/50 1.10kW	MS402	3x400V	DOL	0013HH10	1	--	--	0013H401	1		
13A01902	SP30- 2 Rp3 4"3X380-415/50 2.2kW	MS402	3x400V	DOL	0013HH00	1	--	--	0013H402	1		
13A01903	SP30- 3 Rp3 4"3X380-415/50 3.0kW	MS4000	3x400V	DOL	0013HH00	1	0013HH06	1	0013H403	1		
13A01904	SP30- 4 Rp3 4"3X380-415/50 4.0kW	MS4000	3x400V	DOL	0013HH00	1	0013HH06	2	0013H404	1		
13A01906	SP30- 6 Rp3 4"3X380-415/50 5.5kW	MS4000	3x400V	DOL	0013HH00	1	0013HH06	4	0013H406	1		
13A01908	SP30- 8 Rp3 6"3X380-415/50 7.5kW	MS6000	3x400V	DOL	0013HH01	1	0013HH06	6	0013H608	1		
13A01911	SP30-11 Rp3 6"3X380-415/50 9.2kW	MS6000	3x400V	DOL	0013HH01	1	0013HH06	9	0013H611	1		
13A01913	SP30-13 Rp3 6"3X380-415/50 11kW	MS6000	3x400V	DOL	0013HH01	1	0013HH06	11	0013H613	1		
13A01915	SP30-15 Rp3 6"3X380-415/50 13kW	MS6000	3x400V	DOL	0013HH01	1	0013HH06	13	0013H615	1		
13A01917	SP30-17 Rp3 6"3X380-415/50 15kW	MS6000	3x400V	DOL	0013HH02	1	0013HH06	15	0013H617	1		
13A01921	SP30-21 Rp3 6"3X380-415/50 18.5kW	MS6000	3x400V	DOL	0013HH02	1	0013HH06	19	0013H621	1		
13A01926	SP30-26 Rp3 6"3X380-415/50 22kW	MS6000	3x400V	DOL	0013HH02	1	0013HH06	24	0013H626	1		
13A01931	SP30-31 Rp3 6"3X380-415/50 26kW	MS6000	3x400V	DOL	0013HH02	1	0013HH06	29	0013H631	1		
13A01933	SP30-33 Rp3 6"3X380-415/50 30kW	MS6000	3x400V	DOL	0013HH02	1	0013HH06	31	0013H633	1		
P/N	Descripción	Motor	Tensión	Arranque	Standard Comp. Kit , Rp3" SP46	QTD	Stage Package Kit S46	QTD	Length dependent kits	QTD	Stage kit Reduce imp.	QTD
15A21902	SP46- 2 Rp3 4"3X380-415/50 3.0kW	MS4000	3x400V	DOL	0015HH30	1	--	--	0015H402	1		
15A219F3	SP46- 3C Rp3 4"3X380-415/50 4.0kW	MS4000	3x400V	DOL	0015HH30	1	--	--	0015H403	1	0015HH09	1
15A219F4	SP46- 4C Rp3 4"3X380-415/50 5.5kW	MS4000	3x400V	DOL	0015HH30	1	0015HH06	1	0015H404	1	0015HH09	1
15A21904	SP46- 4 Rp3 6"3X380-415/50 7.5kW	MS6000	3x400V	DOL	0015HH31	1	0015HH06	2	0015H604	1		
15A21905	SP46- 5 Rp3 6"3X380-415/50 7.5kW	MS6000	3x400V	DOL	0015HH31	1	0015HH06	3	0015H605	1		
15A21906	SP46- 6 Rp3 6"3X380-415/50 9.2kW	MS6000	3x400V	DOL	0015HH31	1	0015HH06	4	0015H606	1		
15A21907	SP46- 7 Rp3 6"3X380-415/50 11kW	MS6000	3x400V	DOL	0015HH31	1	0015HH06	5	0015H607	1		
15A21908	SP46- 8 Rp3 6"3X380-415/50 13kW	MS6000	3x400V	DOL	0015HH31	1	0015HH06	6	0015H608	1		
15A219F8	SP46- 8C Rp3 6"3X380-415/50 11kW	MS6000	3x400V	DOL	0015HH31	1	0015HH06	5	0015H608	1	0015HH09	1
15A21910	SP46-10 Rp3 6"3X380-415/50 15kW	MS6000	3x400V	DOL	0015HH31	1	0015HH06	8	0015H610	1		
15A21912	SP46-12 Rp3 6"3X380-415/50 18.5kW	MS6000	3x400V	DOL	0015HH31	1	0015HH06	10	0015H612	1		
15A21915	SP46-15 Rp3 6"3X380-415/50 22kW	MS6000	3x400V	DOL	0015HH32	1	0015HH06	13	0015H615	1		
15A36917	SP46-17 Rp3 6"3X380-415/50 SD 26kW	MS6000	3x400V	DOL	0015HH32	1	0015HH06	15	0015H617	1		
15A21920	SP46-20 Rp3 6"3X380-415/50 30kW	MS6000	3x400V	DOL	0015HH32	1	0015HH06	18	0015H620	1		
15A35324	SP46-24 Rp3 6"3X380-415/50 SD 37kW	MMS6000	3x400V	SD	0015HH32	1	0015HH06	22	0015K624	1		
P/N	Descripción	Motor	Tensión	Arranque	Standard Comp. Kit , Rp4" SP46	QTD	Stage Package Kit SP46	QTD	Length dependent kits	QTD	Stage kit Reduce imp.	QTD
15A55630	SP46-30 R4 8"3X380-415/50 SD 45kW	MMS8000	3x400V	SD								
15A55635	SP46-35 R4 8"3X380-415/50 SD 55kW	MMS8000	3x400V	SD								
15A55637	SP46-37 R4 8"3X380-415/50 SD 63kW	MMS8000	3x400V	SD								
P/N	Descripción	Motor	Tensión	Arranque	Standard Comp. Kit , Rp4" SP60	QTD	Stage Package Kit SP60	QTD	Length dependent kits	QTD	Stage kit Reduce imp.	QTD
14A01902	SP60- 2 Rp4 4"3X380-415/50 4.0kW	MS4000	3x400V	DOL	0014HH00	1	--	--	0014H402	1		
14A01903	SP60- 3 Rp4 4"3X380-415/50 5.5kW	MS4000	3x400V	DOL	0014HH00	1	0014HH06	1	0015H403	1		
14AA1904	SP60- 4 Rp4 6"3X380-415/50 7.5kW	MS6000	3x400V	DOL	0014HH01	1	0014HH06	2	0015H604	1		
14A01905	SP60- 5 Rp4 6"3X380-415/50 9.2kW	MS6000	3x400V	DOL	0014HH01	1	0014HH06	3	0015H605	1		
14A01906	SP60- 6 Rp4 6"3X380-415/50 11kW	MS6000	3x400V	DOL	0014HH01	1	0014HH06	4	0015H606	1		
14A01907	SP60- 7 Rp4 6"3X380-415/50 13kW	MS6000	3x400V	DOL	0014HH01	1	0014HH06	5	0015H607	1		
14A01908	SP60- 8 Rp4 6"3X380-415/50 15kW	MS6000	3x400V	DOL	0014HH01	1	0014HH06	6	0015H608	1		
14A01910	SP60-10 Rp4 6"3X380-415/50 18.5kW	MS6000	3x400V	DOL	0014HH01	1	0014HH06	8	0015H610	1		
14A01912	SP60-12 Rp4 6"3X380-415/50 22kW	MS6000	3x400V	DOL	0014HH01	1	0014HH06	10	0015H612	1		
14A01915	SP60-15 Rp4 6"3X380-415/50 26kW	MS6000	3x400V	DOL	0014HH02	1	0014HH06	13	0015H615	1		
14A01917	SP60-17 Rp4 6"3X380-415/50 30kW	MS6000	3x400V	DOL	0014HH02	1	0014HH06	15	0015H617	1		
14A15320	SP60-20 Rp4 6"3X380-415/50 SD 37kW	MMS6000	3x400V	SD	0014HH02	1	0014HH06	18	0015K620	1		
14AB5321	SP60-21 Rp4 6"3X380-415/50 SD 37kW	MMS6000	3x400V	SD	0014HH02	1	0014HH06	19	0015K621	1		
P/N	Descripción	Motor	Tensión	Arranque	Standard Comp. Kit , Rp5" SP77	QTD	Stage Package Kit SP77	QTD	Length dependent kits	QTD	Stage kit Reduce imp.	QTD
16A01902	SP77- 2 Rp5 6"3X380-415/50 7.5kW	MS6000	3x400V	DOL	0016HH00	1	0016HH06	1	0019H602	1		
16A01903	SP77- 3 Rp5 6"3X380-415/50 11kW	MS6000	3x400V	DOL	0016HH00	1	0016HH06	2	0019H603	1		
16A019C3	SP77- 3B Rp5 6"3X380-415/50 9.2kW	MS6000	3x400V	DOL	0016HH00	1	0016HH06	1	0019H603	1	0016HH02	1
16A01904	SP77- 4 Rp5 6"3X380-415/50 15kW	MS6000	3x400V	DOL	0016HH00	1	0016HH06	3	0019H604	1		
16A019C4	SP77- 4B Rp5 6"3X380-415/50 13kW	MS6000	3x400V	DOL	0016HH00	1	0016HH06	2	0019H604	1	0016HH02	1
16A01905	SP77- 5 Rp5 6"3X380-415/50 18.5kW	MS6000	3x400V	DOL	0016HH00	1	0016HH06	4	0019H605	1		
16A01906	SP77- 6 Rp5 6"3X380-415/50 22kW	MS6000	3x400V	DOL	0016HH00	1	0016HH06	5	0019H606	1		
16A01907	SP77- 7 Rp5 6"3X380-415/50 26kW	MS6000	3x400V	DOL	0016HH00	1	0016HH06	6	0019H607	1		
16A01909	SP77- 9 Rp5 6"3X380-415/50 30kW	MS6000	3x400V	DOL	0016HH01	1	0016HH06	8	0019H609	1		
16AB5311	SP77-11 Rp5 6"3X380-415/50 SD 37kW	MMS6000	3x400V	SD	0016HH01	1	0016HH06	10	0019K611	1		
16A15312	SP77-12 Rp5 8"3X380-415/50 SD 45kW	MMS8000	3x400V	SD	0016HH18	1	0016HH06	11	0019K812	1		
16A00315	SP77-15 Rp5 8"3X380-415/50 55kW	MMS8000	3x400V	SD	0016HH18	1	0016HH06	14	0019K815	1		
16A00318	SP77-18 Rp5 8"3X380-415/50 63kW	MMS8000	3x400V	SD	0016HH18	1	0016HH06	17	0019K818	1		
16A00320	SP77-20 Rp5 8"3X380-415/50 75kW	MMS8000	3x400V	SD	0016HH18	1	0016HH06	19	0019K820	1		
P/N	Descripción	Motor	Tensión	Arranque	Standard Comp. Kit , Rp5" SP95	QTD	Stage Package Kit SP95	QTD	Length dependent kits	QTD	Stage kit Reduce imp.	QTD
19001901	SP95- 1 Rp5 6"3X380-415/50 5.5kW	MS6000	3x400V	DOL	0019HH00	1	--	--	0019H601	1		
19001902	SP95- 2 Rp5 6"3X380-415/50 9.2kW	MS6000	3x400V	DOL	0019HH00	1	0019HH06	1	0019H602	1		
19001902	SP95- 2BB Rp5 6"3X380-415/50 5.5kW	MS6000	3x400V	DOL	0019HH05	1	--	--	0019H602	1	0019HH02	1
19001903	SP95- 3 Rp5 6"3X380-415/50 13kW	MS6000	3x400V	DOL	0019HH00	1	0019HH06	2	0019H603	1		
19001904	SP95- 4 Rp5 6"3X380-415/50 18.5kW	MS6000	3x400V	DOL	0019HH00	1	0019HH06	3	0019H604	1		
190019C4	SP95- 4B Rp5 6"3X380-415/50 15kW	MS6000	3x400V	DOL	0019HH00	1	0019HH06	2	0019H604	1	0019HH02	1
19001905	SP95- 5 Rp5 6"3X380-415/50 22kW	MS6000	3x400V	DOL	0019HH00	1	0019HH06	4	0019H605	1		
19001906	SP95- 6 Rp5 6"3X380-415/50 26kW	MS6000	3x400V	DOL	0019HH00	1	0019HH06	5	0019H606	1		
19001907	SP95- 7 Rp5 6"3X380-415/50 30kW	MS6000	3x400V	DOL	0019HH00	1	0019HH06	6	0019H607	1		
19075309	SP95- 9 Rp5 6"3X380-415/50 SD 37kW	MMS6000	3x400V	SD	0019HH15	1	0019HH06	8	0019K609	1		
19015310	SP95-10 Rp5 8"3X380-415/50 SD 45kW	MMS8000	3x400V	SD	0019HH18	1	0019HH06	9	0019K810	1		
19000313	SP95-13 Rp5 8"3X380-415/50 55kW	MMS8000	3x400V	SD	0019HH18	1	0019HH06	12	0019K813	1		
19000314	SP95-14 Rp5 8"3X380-415/50 63kW	MMS8000	3x400V	SD	0019HH18	1	0019HH06	13	0019K814	1		
19000317	SP95-17 Rp5 8"3X380-415/50 75kW	MMS8000	3x400V	SD	0019HH18	1	0019HH06	16	0019K817	1		
P/N	Descripción	Motor	Tensión	Arranque	Standard Comp. Kit , Rp6" SP125	QTD	Stage Package Kit SP125	QTD	Length dependent kits	QTD	Stage kit Reduce imp.	QTD
17A019A1	SP125- 1A Rp6 6"3X380-415/50 7.5kW	MS6000	3x400V	DOL	0017HH08	1	--	--	0017H601	1		
17A01902	SP125- 2 Rp6 6"3X380-415/50 22kW	MS6000	3x400V	DOL	0017HH00	1	0017HH06	1	0017H602	1		
17A019A2	SP125- 2A Rp6 6"3X380-415/50 18.5kW	MS6000	3x400V	DOL	0017HH00	1						

17A15306	SP125- 6 Rp6 8"3X380-415/50 SD 63kW	MMS8000	3x400V	SD	0017HH13	1	0017HH06	5	0017K806	1		
17A00308	SP125- 8 Rp6 8"3X380-415/50 75kW	MMS8000	3x400V	SD	0017HH13	1	0017HH06	7	0017K808	1		
17A15310	SP125-10 Rp6 8"3X380-415/50 SD 92kW	MMS8000	3x400V	SD	0017HH14	1	0017HH06	9	0017K810	1		
P/N	Descripción	Motor			Standard Comp. Kit , Rp6" SP160	QTD	Stage Package Kit SP160	QTD	Length dependent kits	QTD	Stage kit Reduce imp.	QTD
20021901	SP160- 1 Rp6 6"3X380-415/50 13kW	MS6000	3x400V	DOL	0020HH00	1	--	--	0017H601	1		
200219A1	SP160- 1A Rp6 6"3X380-415/50 9.2kW	MS6000	3x400V	DOL	0020HH08	1	--	--	0017H601	1	0020HH07	1
20021902	SP160- 2 Rp6 6"3X380-415/50 26kW	MS6000	3x400V	DOL	0020HH00	1	0020HH06	1	0017H602	1		
200219A2	SP160- 2A Rp6 6"3X380-415/50 22kW	MS6000	3x400V	DOL	0020HH00	1	--	--	0017H602	1	0020HH07	1
200219B2	SP160- 2AA Rp6 6"3X380-415/50 18.5kW	MS6000	3x400V	DOL	0020HH08	1	--	--	0017H602	1	0020HH07	1
200219B3	SP160- 3AA Rp6 6"3X380-415/50 30kW	MS6000	3x400V	DOL	0020HH00	1	0020HH06	1	0017H603	1	0020HH07	2
20035303	SP160- 3 Rp6 6"3X380-415/50 SD 37kW	MMS6000	3x400V	SD	0020HH12	1	0020HH06	2	0017K603	1		
200353A4	SP160- 4A Rp6 8"3X380-415/50 SD 45kW	MMS8000	3x400V	SD	0020HH13	1	0020HH06	2	0017K804	1	0020HH07	2
200353A5	SP160- 5A Rp6 8"3X380-415/50 SD 55kW	MMS8000	3x400V	SD	0020HH13	1	0020HH06	3	0017K805	1	0020HH07	1
20035306	SP160- 6 Rp6 8"3X380-415/50 SD 75kW	MMS8000	3x400V	SD	0020HH13	1	0020HH06	5	0017K806	1		
200353B6	SP160- 6AA Rp6 8"3X380-415/50 SD 63kW	MMS8000	3x400V	SD	0020HH13	1	0020HH06	3	0017K806	1	0020HH07	2
200353B7	SP160- 7AA Rp6 8"3X380-415/50 SD 75kW	MMS8000	3x400V	SD	0020HH13	1	0020HH06	4	0017K807	1	0020HH07	2
20020308	SP160- 8 Rp6 8"3X380-415/50 92kW	MMS8000	3x400V	SD	0020HH13	1	0020HH06	7	0017K808	1		
P/N	Descripción	Motor			Standard Comp. Kit , Rp6" SP215	QTD	Stage Package Kit SP215	QTD	Length dependent kits	QTD	Stage kit Reduce imp.	QTD
18A01901	SP215- 1 Rp6 6"3X380-415/50 18.5kW	MS6000	3x400V	DOL	0018HH00	1	--	--	0018H601	1		
18A019A1	SP215- 1A Rp6 6"3X380-415/50 15kW	MS6000	3x400V	DOL	0018HH08	1	--	--	0018H601	1		
18A219B2	SP215- 2AA Rp6 6"3X380-415/50 30kW	MS6000	3x400V	DOL	0018HH08	1	--	--	0018H602	1	0018HH07	1
18A15302	SP215- 2 Rp6 6"3X380-415/50 SD 45kW	MMS8000	3x400V	SD	0018HH01	1	0018HH06	1	0018K802	1		
18A353A2	SP215- 2A Rp6 6"3X380-415/50 SD 37kW	MMS6000	3x400V	SD	0018HH00	1	--	--	0018K602	1	0018HH07	1
18A15303	SP215- 3 Rp6 8"3X380-415/50 SD 63kW	MMS8000	3x400V	SD	0018HH01	1	0018HH06	2	0018K803	1		
18A153A3	SP215- 3A Rp6 8"3X380-415/50 SD 55kW	MMS8000	3x400V	SD	0018HH01	1	0018HH06	1	0018K803	1	0018HH07	1
18A15304	SP215- 4 Rp6 8"3X380-415/50 SD 75kW	MMS8000	3x400V	SD	0018HH01	1	0018HH06	3	0018K804	1		
18A15305	SP215- 5 Rp6 8"3X380-415/50 SD 92kW	MMS8000	3x400V	SD	0018HH01	1	0018HH06	4	0018K805	1		